## WHY DURAN VOLUMETRIC GLASSWARE?

1. DURAN® VOLUMETRIC INSTRUMENTS: ACHIEVING PRECISION THROUGH QUALITY

DURAN

2. FOR THE HIGHEST DEMANDS: QUALITY RIGHT DOWN THE LINE

Cover all applications from measuring liquid amounts, diluting solutions or mixing several components.

3. DURAN® LABORATORY GLASSWARE: END-TO-END PRODUCTION FROM A SINGLE SOURCE

All DURAN volumetric glassware manufactured in-house with mixture preparation for the borosilicate glass 3.3., from glass melting through to calibration.

4. GUARANTEED: ALL OPTIONS COVERED

Unrestricted choice – The range of products on offer covers all accuracy classes including the associated certificates and glass specifications

Outstanding print quality - Emphasises the most important information such as volume specification, accuracy class and standard taper joint details

Clear labelling - Batch numbers are clearly printed on the glass, while individual numbers are laser-etched onto the base of the volumetric flask

Also includes the new ergonomically shaped stoppers for straightforward and reliable opening and closing.

## 5. ALL INFORMATION AT A GLANCE

PRECISE DIFFERENTIATION: TWO ACCURACY CLASSES Available in 3 accuracy classes, which are A, AS and B.

> 7. QUALITY EXPRESSED IN COLOUR High-contrast colour code is used. For example:

Accuracy class A, clear glass: Printed in blue.

Accuracy class A, amber glass: Printed in white.

Accuracy class B, Clear glass only: Printed in white.

8. CERTIFICATES: TEST RESULTS CLEARLY DEMONSTRATED
- Conformity mark DE-M

- Batch certificate
- Individual certificate
- USP individual certificate





e-mail: sals@sentori.com.my website: www.sentori.com.my

